



LUBRICATE WITH " MOLY-TEF "
THE COMPONENT :N°

FOR NOT SPECIFIED
TIGHTENING TORQUES
SEE NPF 086

10	1	PIASTRA MOBILE P508M A 4 MASCHI FFN	48300100000022	
9	1	SP.EL.BASE08-7 POLI X P.MOBILE	CORSPEL08-7 M	
8	3	MASCHIO 3FFNP12 MULTIFASTER	3FFNP12-12S M	34
7	2	DADO AUTOBLOCCANTE M8 ISO 7044	15400800008000	
6	2	SPINA DI GUIDA PIASTRE	48300210000000	
5	2	RULLINI PIASTRA P8 COLD DEFF	48300281000011	
4	2	VITE M8X30,5 DEFORMATA A FREDDO	48300133000030	
3	3	VITI AUTOFIL.TRILOBATE M3X12 CROCE	48300440000000	
2	2	OR NITRILE 70° SHORE (SPINA P) x NPF075	OR2,62x9,19 M	
1	1	ETICHETTA FASTER 53x18	ET002	
POS.	Q.TY	Description	Drawing No.	HEX

Faster RIVOLTA D'ADDA-CR-ITALY		THIS DRAWING IS EXCLUSIVE PROPERTY OF FASTER S.p.A ANY UNAUTHORIZED COPY AND/OR USE ARE STRICTLY PROHIBITED.	
DRAWN	CONFIGURATOR	GENERAL TOLERANCES (UNLESS OTHERWISE SPECIFIED): LINEAR DIMENSIONS: 0.1 ANGULAR DIMENSIONS: 1+ RADIUS AND CHAMFER: 0.05 SHARP EDGES NOT DIMENSIONED; RADIUS OR CHAMFER MAX. 0.2	
DATE	24/10/2022		
SIZE	A2	DESCRIPTION	
DIM. MILLIMETERS		MULTIFASTER MOBILE PART	
		DIMENSION	SYMBOL
		CRITICAL	
		IMPORTANT	
		SECONDARY	NO SYMBOL
PART NUMBER :		REVISION	
MF-P508 M=004645=M		A 10	
DRAWING N°		DRAWING N°	
DB_MF-P508 M-004645-M		DB_MF-P508 M-004645-M	