



LUBRICATE WITH " MOLY-TEF "  
THE COMPONENT :N° 2

FOR NOT SPECIFIED  
TIGHTENING TORQUES  
SEE NPF 086

10	1	PIASTRA MOBILE P508M A 4 MASCHI FFN	48300100000022	
9	1	SP.EL.BASE08-7 POLI X P.MOBILE	CORSPEL08-7 M	
8	3	MASCHIO 3FFNP12 MULTIFASTER	3FFNP12-12S M	34
7	2	DADO AUTOBLOCCANTE M8 ISO 7044	15400800008000	
6	2	SPINA DI GUIDA PIASTRE	48300210000000	
5	2	RULLINI PIASTRA P8 COLD DEFF	48300281000011	
4	2	VITE M8X30,5 DEFORMATA A FREDDO	48300133000030	
3	3	VITI AUTOFIL.TRILOBATE M3X12 CROCE	48300440000000	
2	2	OR NITRILE 70° SHORE (SPINA P) x NPF075	OR2,62x9,19 M	
1	1	ETICHETTA FASTER 53x18	ET002	
POS.	Q.TY	Description	Drawing No.	HEX

<b>Faster</b> RIVOLTA D'ADDA-CR-ITALY		<small>THIS DRAWING IS EXCLUSIVE PROPERTY OF FASTER S.p.A ANY UNAUTHORIZED COPY AND/OR USE ARE STRICTLY PROHIBITED.</small>		
DRAWN	CONFIGURATOR	DESCRIPTION MULTIFASTER MOBILE PART		
DATE	24/10/2022			
SIZE	A2	GENERAL TOLERANCES (UNLESS OTHERWISE SPECIFIED): LINEAR DIMENSIONS '0.1 ANGULAR DIMENSIONS '1+ RADIUS AND CHAMFER '0.05 SHARP EDGES NOT DIMENSIONED; RADIUS OR CHAMFER MAX. 0.2	PART NUMBER :	
	DIM. MILLIMETERS	CRITICAL	MF-P508 M=004645=M	
		IMPORTANT	DRAWING N°	
		SECONDARY	NO SYMBOL	REVISION
			DB_MF-P508 M-004645-M	A 10